

Flexhead® Flexible Pipe

Flexibility for Designers & Installers



Flexhead® Flexible Pipe (FFP) products are stainless steel hoses and available with SLT coupling connections. Available in lengths of 24" (bends up to 90°) and 48" (bends up to 180°) with OD of 2", 2 ½", 3" and 4". Pressure rating for 2", 2 ½", and 3" is 300PSI and 4" at 250PSI. An easy, cost effective, and a quickway to connect pipes at odd angles or to reduce the number of couplings and fittings required.

Friction Loss Data

Feet of Pipe	24" Straight	24" 90°	48" Straight	48"90°	48" U-Bend
2"	8.4	16.9	16.6	27.8	33.9
2.5"	8.8	13.4	16.5	21.9	26.3
3"	9.9	16.7	22.9	31.3	36.7
4"	9.7	17	19.9	27.7	33.6

Note: Feet of Schedule 40 pipe of equivalent nominal size.

For more information or for product samples contact your local ASC Engineered Solutions sales representative.

Features & Benefits

- Off the shelf option for uncommon angles
- Low friction loss number
- Available with ASC SLT technology
- Saves time and money
- Provides standard groove pipe connection
- · Reduce install time
- Allows for more flexibility in piping design







